



YHSQ14F11X02D

by Burndy
Catalog ID: YHSQ14F11X02D

Cu Heat Shrink Insul Female Quick Disconnect, 14-16 AWG, 1.42" L, 0.11" W, Serrated bbl, Red(Insul Color).

Features: Made From Pure Copper, Annealed For Maximum Strength, Color-Coded, Imprinted With Wire Size, Serrated Barrels Offer Maximum Wire Contact And Tensile Strength, Electro Tin Plated For Corrosion Resistance, Wire Strip Length 5/16 IN, Conductor Strip Length: 5/16 IN

Product Details

General

Application	For Use On Copper Conductor
Connector Type	Female Disconnect
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS
UPC	781810525432

Dimensions

Dimension - B Length inch	0.17 in
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.42 in
Dimension - Pad Width inch	0.11 in
Dimension - Strip Length inch	5/16

Conductor Related

Conductor - Copper Str Size Range	18 AWG - 22 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200 EA
-----------------	---------

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)