



YHSS10BG10

by Burndy
Catalog ID: YHSS10BG10

Copper Butt Splice, 12 - 10 AWG, Tin Plated, Nylon Insulation

Product Details

General

Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810486634

Dimensions

Dimension - Length Overall inch	1.60 in
---------------------------------	---------

Conductor Related

Conductor - Copper Solid Size	12;11;10
Conductor - Copper Solid Size Range	12-10
Conductor - CopperWeld C Solid Size	12;10
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)