



## YHSS18BG10

by Burndy  
Catalog ID: YHSS18BG10

Copper Butt Splice, 22 - 18 AWG, Tin Plated, Nylon Insulation

### Product Details

#### General

Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810486672

#### Dimensions

Dimension - Length Overall inch	1.50 in
---------------------------------	---------

#### Conductor Related

Conductor - Copper Solid Size	20;18
Conductor - Copper Solid Size Range	20-18
Conductor - CopperWeld C Solid Size	20;18
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)