

YJA2/OT38

by Burndy
Catalog ID: YJA2/OT38

Copper CSA Lugs; 1 Hole; 2/0 AWG Code; 600V-35kV; 3/8" stud; Long; Compression; 0.56 in BCD



* Representative image

Product Details

General

| | |
|----------------------------------|----------------------|
| Connector Type | Terminal |
| Feature - Barrel Type | Standard |
| Material | Aluminum |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| UPC | 621945258358 |
| UPC 12 Digit | 6219452583588 |

Dimensions

| | |
|-----------------------------------|----------|
| Physical Attribute - Tongue Angle | Straight |
|-----------------------------------|----------|

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |

| |
|-----------|
| UL Listed |
|-----------|

| |
|----|
| No |
|----|

Logistics

| |
|-----------------------|
| Minimum Pack Quantity |
|-----------------------|

| |
|-----|
| 144 |
|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)