

YKA292N

by Burndy
Catalog ID: YKA292N

Prop 65 Notice

HYLUG™, Tin plated Copper Compression disconnectable terminal with fixed H/W, 250 Kcmil, 1/2 IN Stud, 169 Index, For making disconnectable tap or jumper connections



Product Details

General

Connector Type	Terminal
Die Index	169
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810081099

Dimensions

Dimension - B Length fraction	1-64/79 in
Dimension - B Length inch	1.81 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.52 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.33 in
Dimension - Strip Length inch	1- 7/8 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)