

YKA302N

by Burndy
Catalog ID: YKA302N

Prop 65 Notice

HYLUG™, Copper Disconnectable Compression Terminal, With Fixed H/W, 2 Holes, 300 KCMIL Cu, 1/2" Stud



Product Details

General

Connector Type	Terminal
Die Index	170
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	621945437371

Dimensions

Dimension - B Length fraction	1-22/31 in
Dimension - B Length inch	1.71 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	141 mm
Dimension - Length Overall inch	5.54 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.05 in
Dimension - Pad Width inch	1.42 in
Dimension - Strip Length inch	1- 13/16 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	300 kcmil
Conductor - Copper Str Size Range	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)