

YKA321ACG1

by Burndy
Catalog ID: YKA321ACG1

Prop 65 Notice

CAST AL. TERMINAL



Product Details

General

Connector Type	Terminal
Die Index	317;M
Material	Copper
Oxide Inhibitor Type	Penetrox A
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	Y
UPC	781810468289
UPC 12 Digit	7818104682899

Dimensions

Dimension - B Length fraction	3-3/50 in
Dimension - B Length inch	3.06 in
Dimension - D inch	3 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.72 in
Dimension - L Length Overall mm	182 mm
Dimension - Length Overall inch	7.16 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	3 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)