

# YKA6C2N

by Burndy  
Catalog ID: YKA6C2N

Prop 65 Notice

HYLUG™, Copper Disconnectable Compression Terminal, With Fixed H/W, 2 Holes, #6 STR Cu, 1/2" Stud



## Product Details

### General

Connector Type	Terminal
Die Index	163
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
UPC	781810000434

### Dimensions

Dimension - B Length fraction	1-4/57 in
Dimension - B Length inch	1.07 in
Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	129 mm
Dimension - Length Overall inch	5.06 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.5 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	1- 3/16 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	40
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)