

YNA32R154N

by Burndy
Catalog ID: YNA32R154N



Product Details

General

Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810491317
UPC 12 Digit	7818104913177

Dimensions

Dimension - L Length Overall mm	233 mm
Dimension - Length Overall inch	9.16 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in

Conductor Related

Conductor - ACAR Str Size	400 (19)
Conductor - ACSR Str Size	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size	336.4;350

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)