

YNA34R

by Burndy
Catalog ID: YNA34R

Prop 65 Notice

HYLUG™, Aluminum Tube Compression Terminal, 2 Holes, 397.5 Kcmil ACSR, 397.5 - 477 Kcmil Al, 230 kV, 1.75" Spacing, Die Index: 719



Product Details

General

Connector Type	Terminal
Die Index	719
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016183
UPC 12 Digit	7818100161833

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	231 mm
Dimension - Length Overall inch	9.08 in
Dimension - Outside Diameter inch	1.3 in
Dimension - Pad Width inch	1.78 in
Dimension - Width fraction	1.78 in

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee-397.5 (30/7) Larkspur
Conductor - AL Str Size	397.5;400;450;477
Conductor - AL Str Size Range	397.5-477

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)