

YNA36R90

by Burndy
Catalog ID: YNA36R90

Prop 65 Notice

HYLUG™, Aluminum Compression terminal for ACSR and Stranded aluminum cable, 477 Kcmil ACSR, 500-556.5 Kcmil Aluminum cable, 90 Degree



Product Details

General

Connector Type	Terminal
Material	Aluminum
Physical Attribute - Pad Orientation	90 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810157794
UPC 12 Digit	7818101577944

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.7 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican-477.0 (30/7) Hen
Conductor - AL Str Size	500;550;556.5
Conductor - AL Str Size Range	500-556.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)