

YNA36R

by Burndy
Catalog ID: YNA36R

Prop 65 Notice

HYLUG™, Aluminum Tube Compression Terminal, 2 Holes, 477 Kcmil ACSR, 500 - 556.5 Kcmil Al, 230 kV, 1.75" Spacing



Product Details

General

Connector Type	Terminal
Die Index	720
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810822005
UPC 12 Digit	7818108220055

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	241 mm
Dimension - Length Overall inch	9.47 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	1.96 in
Dimension - Width fraction	1.96 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican-477.0 (30/7) Hen
Conductor - AL Str Size	500;550;556.5
Conductor - AL Str Size Range	500-556.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)