

YNA39R4N

by Burndy
Catalog ID: YNA39R4N

Prop 65 Notice

HYLUG™, Aluminum Compression Terminal, 556.5 Kcmil ACSR, 600-650 Kcmil Aluminum, 634.9-653.1 Kcmil ACAR, 230 Kv, 722 Index



Product Details

General

Connector Type	Terminal
Die Index	722
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810042465
UPC 12 Digit	7818100424655

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	248 mm
Dimension - Length Overall inch	9.76 in
Dimension - Outside Diameter inch	1.56 in
Dimension - Pad Width inch	3 in
Dimension - Width fraction	3.00 in

Conductor Related

Conductor - ACAR Str Size	634.9 - 653.1 KCMIL
Conductor - ACAR Str Size Range	634.9 - 653.1 KCMIL
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (30/7) Eagle kcmil
Conductor - AL Str Size	600 kcmil;636 kcmil;650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)