

YNA39RTH

by Burndy
Catalog ID: YNA39RTH

Prop 65 Notice

Aluminum Compression terminal, 556.5 kcmil, 345 kV



Product Details

General

Connector Type	Terminal
Die Index	722
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810055014
UPC 12 Digit	7818100550144

Dimensions

Dimension - L Length Overall mm	256 mm
Dimension - Length Overall inch	10.09 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.08 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican-477.0 (30/7) Hen
Conductor - AL Str Size	500;550;556.5
Conductor - AL Str Size Range	500-556.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	15
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)