



YNA43R45

by Burndy
Catalog ID: YNA43R45

Prop 65 Notice

Aluminum Compression Terminal 230 kV, 605-666.6 kcmil ACSR, 700-800 kcmil Alum., 45 Deg

Product Details

General

Connector Type	Terminal
Die Index	724
Material	Aluminum
Physical Attribute - Pad Orientation	45 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810283929
UPC 12 Digit	7818102839299

Dimensions

Dimension - B Length inch	4.53 in
Dimension - Height fraction	6-13/50 in
Dimension - Height inch	6.26 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.51 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.07 in

Conductor Related

Conductor - ACSR Str Size	605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)