



YNA43R90

by Burndy
Catalog ID: YNA43R90

Prop 65 Notice

HYLUG™, Aluminum Compression terminal for ACSR and Stranded aluminum cable, 605-666.5 Kcmil ACSR, 700-800 Kcmil Aluminum cable, 90 Degree

Product Details

General

Connector Type	Terminal
Die Index	724
Material	Aluminum
Physical Attribute - Pad Orientation	90 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810221945
UPC 12 Digit	7818102219455

Dimensions

Dimension - B Length inch	4.88 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Dimension - L Length Overall mm	155 mm
Dimension - Length Overall inch	6.09 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3 in
Dimension - Width fraction	3.00 in

Conductor Related

Conductor - ACSR Str Size	605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)