

# YNA43RT15

by Burndy  
Catalog ID: YNA43RT15



## Product Details

### General

Connector Type	Terminal
Die Index	724
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Trade Name	HYLUG™
UPC	781810485194
UPC 12 Digit	7818104851944

### Dimensions

Dimension - L Length Overall mm	259 mm
Dimension - Length Overall inch	10.21 in
Dimension - Length Side A inch	10.21 in
Dimension - Length Side B inch	10.32 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

### Conductor Related

Conductor - ACSR Str Size	605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

### Logistics

Minimum Pack Quantity	3
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)