

# YNA451R15H

by Burndy  
Catalog ID: YNA451R15H

Prop 65 Notice

Comprsn Terminal For ACSR,ACAR and std Al Cable with Hardware Kit,  
725 Index



## Product Details

### General

Connector Type	Terminal
Die Index	725
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810180280
UPC 12 Digit	7818101802800

### Dimensions

Dimension - L Length Overall mm	259 mm
Dimension - Length Overall inch	10.21 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in

### Conductor Related

Conductor - ACAR Str Size	800 (37);850 (37);900 (37)
Conductor - ACAR Str Size Range	800 (37)-900 (37)
Conductor - ACSR Str Size	715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane
Conductor - AL Str Size	795.5;800;874.5;900;954;1000
Conductor - AL Str Size Range	795.5-1000

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)