



YNA451RT15H

by Burndy
Catalog ID: YNA451RT15H

Prop 65 Notice

HYLUG™, Aluminum Compression Terminal, 715.5-874.5 Kcmil ACSR, 795-1000 Kcmil Aluminum, 840-927.2 Kcmil ACAR, 15 Degree, Hardware included

Product Details

General

| | |
|--------------------------------------|---------------|
| Connector Type | Terminal |
| Die Index | 725 |
| Material | Aluminum |
| Physical Attribute - Pad Orientation | 15 Degree |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYLUG™ |
| UPC | 781810104194 |
| UPC 12 Digit | 7818101041944 |

Dimensions

| | |
|--|----------|
| Dimension - Bolt Hole Size inch | 0.56 in |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm | 271 mm |
| Dimension - Length Overall inch | 10.65 in |
| Dimension - Outside Diameter inch | 1.8 in |
| Dimension - Pad Width inch | 3.22 in |
| Dimension - Width fraction | 3.22 in |

Conductor Related

| | |
|---------------------------------|---|
| Conductor - ACAR Str Size | 840.2 KCMIL - 927.2 KCMIL |
| Conductor - ACAR Str Size Range | 840.2 KCMIL - 927.2 KCMIL |
| Conductor - ACSR Str Size | 715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane |
| Conductor - ACSR Str Size Range | 715.5 (54/7) Crow-874.5 (54/7) Crane |
| Conductor - AL Str Size | 795.5;800;874.5;900;954;1000 |
| Conductor - AL Str Size Range | 795.5-1000 |

Certifications and Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)