

YNA49R15

by Burndy
Catalog ID: YNA49R15

Prop 65 Notice

HYLUG™, Aluminum Compression Terminal for ACSR, ACAR & SAC Cables, 900-1113 Kcmil ACSR, 1033.5-1272 Kcmil SAC, 983.1-1198 Kcmil ACAR, 250 Kv Max., 10.35 IN L, 4 hole, 15 Deg



Product Details

General

Connector Type	Terminal
Die Index	727
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810367766
UPC 12 Digit	7818103677666

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	263 mm
Dimension - Length Overall inch	10.35 in
Dimension - Length Side A inch	10.35 in
Dimension - Length Side B inch	10.46 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

Conductor Related

Conductor - ACAR Str Size	983.1 KCMIL - 1198 KCMIL
Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACSR Str Size	900 (54/7) Canary; 954 (54/7) Cardinal; 1033.5 (54/7) Curlew; 1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch
Conductor - AL Str Size	1033.5; 1100; 1192.5; 1200; 1272.2
Conductor - AL Str Size Range	1033.5-1272.2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)