

# YNA49R90

by Burndy  
Catalog ID: YNA49R90

Prop 65 Notice

HYLUG™, Aluminum Compression Terminal , 900-1113 kcmil ACSR 45-7STR 1033.5-1272 kcmil ALUM., 90 Degree



## Product Details

### General

Connector Type	Terminal
Die Index	727
Material	Aluminum
Physical Attribute - Pad Orientation	90 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810283974
UPC 12 Digit	7818102839744

### Dimensions

Dimension - B Length inch	4.88 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.19 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3 in
Dimension - Width fraction	3.00 in

### Conductor Related

Conductor - ACSR Str Size	900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch
Conductor - AL Str Size	1033.5;1100;1192.5;1200;1272.2
Conductor - AL Str Size Range	1033.5-1272.2

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)