



YNA49RT2N

by Burndy
Catalog ID: YNA49RT2N

Prop 65 Notice

HYLUG™, Aluminum Compression terminal, 900-1113 Kcmil ACSR, 1033.5-1272 Kcmil Aluminum, 983.1-1198 Kcmil ACAR, Cable to flat, 2 hole, Extrahigh voltage applications

Product Details

General

Connector Type	Terminal
Die Index	727
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810419311
UPC 12 Digit	7818104193111

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	274 mm
Dimension - Length Overall inch	10.77 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	2.74 in
Dimension - Width fraction	2.74 in

Conductor Related

Conductor - ACAR Str Size	983.1 KCMIL - 1198 KCMIL
Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACSR Str Size	900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch
Conductor - AL Str Size	1033.5;1100;1192.5;1200;1272.2
Conductor - AL Str Size Range	1033.5-1272.2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)