



## YNA49RT

by Burndy  
Catalog ID: YNA49RT

Prop 65 Notice

Compression Terminal , 900-1113 kcmil ACSR 45-7STR 1033.5-1272 kcmil ALUM.983.1-1198 kcmil ACAR ., 4 Pad holes, 10-1/2 in Length.

Features:Compression Terminal for ACSR Conductor

## Product Details

### General

Application	For use on: ACSR, ACAR and SAC Transmission Lines
Connector Type	Terminal
Die Index	727
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YNA-RT EHV
UPC	781810016367
UPC 12 Digit	7818100163677

### Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	274 mm
Dimension - Length Overall inch	10.77 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

### Conductor Related

Conductor - ACAR Str Size	983.1 KCMIL - 1198 KCMIL
Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACSR Str Size	900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch
Conductor - AL Str Size	1033.5;1100;1192.5;1200;1272.2
Conductor - AL Str Size Range	1033.5-1272.2

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)