



YNA52R15H

by Burndy
Catalog ID: YNA52R15H

Prop 65 Notice

Comprsn Terminal For ACSR,ACAR and std Al Cable with Hardware Kit,
728 Index

Product Details

General

| | |
|--------------------------------------|---------------|
| Connector Type | Terminal |
| Die Index | 728 |
| Material | Aluminum |
| Physical Attribute - Pad Orientation | 15 Degree |
| Trade Name | HYLUG™ |
| UPC | 781810490037 |
| UPC 12 Digit | 7818104900377 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - L Length Overall mm | 307 mm |
| Dimension - Length Overall inch | 12.09 in |
| Dimension - Outside Diameter inch | 2.26 in |
| Dimension - Pad Width inch | 3.22 in |

Conductor Related

| | |
|---------------------------|--|
| Conductor - ACAR Str Size | 1250 (61);1300 (61) |
| Conductor - ACSR Str Size | 1113 (54/19) Finch;1272 (54/19) Pheasant |
| Conductor - AL Str Size | 1351.5;1400;1431.0;1500 |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)