

YNA52R15

by Burndy
Catalog ID: YNA52R15

Prop 65 Notice

HYLUG™, Aluminum Compression terminal, 1113.54-1351.5 Kcmil
ACSR,1351.5-1510 Kcmil SAC,1277-1280 Kcmil ACAR , 250 Kv Max., 12.09 IN
L, Pad coated W/ oxide retardant



Product Details

General

Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810081563
UPC 12 Digit	7818100815633

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	307 mm
Dimension - Length Overall inch	12.09 in
Dimension - Length Side A inch	12.09 in
Dimension - Length Side B inch	12.24 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

Conductor Related

Conductor - ACAR Str Size	1277 KCMIL- 1280 KCMIL
Conductor - ACAR Str Size Range	1277 KCMIL- 1280 KCMIL
Conductor - ACSR Str Size	1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil;1351.5 (54/19) Martin kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Finch kcmil-1351.5 (54/19) Martin kcmil
Conductor - AL Str Size	1351.5;1400;1431.0;1500
Conductor - AL Str Size Range	1351.5-1500

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)