

# YNA52RT15

by Burndy  
Catalog ID: YNA52RT15

Prop 65 Notice

HYLUG™, Aluminum Compression Terminal, 345 Kv, 1113.54-1351.5 Kcmil ACSR, 1351.5-1510 Kcmil Aluminum, 1277-1280 Kcmil ACAR, Cable to Flat, 15 Deg



## Product Details

### General

Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016404
UPC 12 Digit	7818100164044

### Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	321 mm
Dimension - Length Overall inch	12.62 in
Dimension - Length Side A inch	12.62 in
Dimension - Length Side B inch	13.82 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

### Conductor Related

Conductor - ACAR Str Size	1277 KCMIL- 1280 KCMIL
Conductor - ACAR Str Size Range	1277 KCMIL- 1280 KCMIL
Conductor - ACSR Str Size	1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil;1351.5 (54/19) Martin kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Finch kcmil-1351.5 (54/19) Martin kcmil
Conductor - AL Str Size	1351.5;1400;1431.0;1500
Conductor - AL Str Size Range	1351.5-1500

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)