

# YNA52RT30

by Burndy  
Catalog ID: YNA52RT30

Prop 65 Notice

Aluminum Compression terminal, 1113-1351.5 kcmil, 345 kV



## Product Details

### General

Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Pad Orientation	30 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810046272
UPC 12 Digit	7818100462722

### Dimensions

Dimension - B Length inch	6.36 in
Dimension - L Length Overall mm	308 mm
Dimension - Length Overall inch	12.11 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in

### Conductor Related

Conductor - ACSR Str Size	1113 (54/19) Finch;1272 (54/19) Pheasant
Conductor - ACSR Str Size Range	1113 (54/19) Finch-1272 (54/19) Pheasant
Conductor - AL Str Size	1351.5;1400;1431.0;1500
Conductor - AL Str Size Range	1351.5-1500

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)