



## YNA54RR4T

by Burndy  
Catalog ID: YNA54RR4T

Prop 65 Notice

HYLUG™, Al Compression Terminal, 1431 Kcmil ACSR, 1590-1600 Kcmil Aluminum, 1534 Kcmil Str., 4 Pad Holes, Extra High Voltage Applications, 345 Kv

## Product Details

### General

|                                      |               |
|--------------------------------------|---------------|
| Connector Type                       | Terminal      |
| Die Index                            | 728           |
| Material                             | Aluminum      |
| Physical Attribute - Pad Orientation | Straight      |
| Prefilled Oxide Inhibitor            | Y             |
| Trade Name                           | HYLUG™        |
| UPC                                  | 781810301272  |
| UPC 12 Digit                         | 7818103012722 |

### Dimensions

|  |          |
|--|----------|
| Dimension - Bolt Hole Size inch              | 0.56 in  |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm              | 362 mm   |
| Dimension - Length Overall inch              | 14.27 in |
| Dimension - Outside Diameter inch            | 2.26 in  |
| Dimension - Pad Width inch                   | 4 in     |
| Dimension - Width fraction                   | 4.00 in  |

### Conductor Related

|                                 |                           |
|---------------------------------|---------------------------|
| Conductor - ACAR Str Size       | 1534 KCMIL                |
| Conductor - ACAR Str Size Range | 1534 KCMIL                |
| Conductor - ACSR Str Size       | 1431 (54/19) Plover kcmil |
| Conductor - ACSR Str Size Range | 1431 (54/19) Plover kcmil |
| Conductor - AL Str Size         | 1590 kcmil - 1600 kcmil   |
| Conductor - AL Str Size Range   | 1590 kcmil-1600 kcmil     |

### Certifications and Compliance

|                               |    |
|-------------------------------|----|
| Certification - CSA Approved  | No |
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 0 |
|-----------------------|---|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)