



YNA54RT

by Burndy
Catalog ID: YNA54RT

Prop 65 Notice

HYLUG™, Al Tube Compression Terminal, 4 Holes, 1431 Kcmil ACSR, 1590 - 1600 Kcmil Al, 1534 Kcmil ACAR, greater than 230 kV, 1.75" Spacing

Product Details

General

Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016398
UPC 12 Digit	7818100163988

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	350 mm
Dimension - Length Overall inch	13.79 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

Conductor Related

Conductor - ACAR Str Size	1534 KCMIL
Conductor - ACAR Str Size Range	1534 KCMIL
Conductor - ACSR Str Size	1431 (54/19) Plover
Conductor - ACSR Str Size Range	1431 (54/19) Plover
Conductor - AL Str Size	1590 kcmil - 1600 kcmil
Conductor - AL Str Size Range	1590 kcmil - 1600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)