

YNA58RT45

by Burndy
Catalog ID: YNA58RT45

Prop 65 Notice

HYLUG™, Al Tube Compression Terminal, operates 345 Kv, 1780 Kcmil ACSR, 2000 Kcmil Aluminum, Cable to flat, For use on extrahigh voltage applications, 45 Deg



Product Details

General

Connector Type	Terminal
Die Index	735
Material	Aluminum
Physical Attribute - Pad Orientation	45 Degree Angle
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810283943
UPC 12 Digit	7818102839433

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	348 mm
Dimension - Length Overall inch	13.7 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.47 in
Dimension - Width fraction	3.47 in

Conductor Related

Conductor - ACSR Str Size	1780 (54/19) kcmil
Conductor - ACSR Str Size Range	1780 (54/19) kcmil
Conductor - AL Str Size	2000 kcmil
Conductor - AL Str Size Range	2000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)