

YNA594RT90

by Burndy
Catalog ID: YNA594RT90

Prop 65 Notice

Aluminum Compression terminal, 2156-2167 kcmil, 345 kV



Product Details

General

Connector Type	Terminal
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	90 Degree Angle
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810180488
UPC 12 Digit	7818101804888

Dimensions

Dimension - B Length inch	7.88 in
Dimension - L Length Overall mm	242 mm
Dimension - Length Overall inch	9.53 in
Dimension - Outside Diameter inch	2.6 in
Dimension - Pad Width inch	3.75 in

Conductor Related

Conductor - ACSR Str Size	2300
Conductor - ACSR Str Size Range	2300
Conductor - AL Str Size	2500
Conductor - AL Str Size Range	2500

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)