



YNA59RT15

by Burndy
Catalog ID: YNA59RT15

Prop 65 Notice

HYLUG™, Compression terminal for ACSR, ACAR and AAC, 2156-2167 Kcmil ACSR, 2250-2300 Kcmil Aluminum, Cable to Flat, 15 Deg

Product Details

General

Connector Type	Terminal
Die Index	735
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree Angle
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810141120
UPC 12 Digit	7818101411200

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	349 mm
Dimension - Length Overall inch	13.75 in
Dimension - Length Side A inch	13.75 in
Dimension - Length Side B inch	13.54 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.57 in
Dimension - Width fraction	3.57 in

Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2250 kcmil;2300 kcmil
Conductor - AL Str Size Range	2250 kcmil-2300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)