



YNA59RT

by Burndy
Catalog ID: YNA59RT

Prop 65 Notice

Al Tube Compression Terminal, 4 Holes, 2156 -2167 Kcmil ACSR, 2250 - 2300 Kcmil Al, greater than 230 kV, 1.75" Spacing.

Features: Compression Terminal ACAR And Stranded Aluminum Cable, For Transmission Lines Over 230 KV, Two Hole NEMA Supplied On Tongue Through 650 KCMIL Aluminum, Four Hole NEMA Supplied On Larger Sizes, When Used With YTW Deadends The 15 DEG Angle Tongue Provides Either A 0 DEG Or 30 DEG Tap, Uses Same Dies As Equivalent Full-Tension Sleeve Or Deadend, Barrel Pre-Filled With PENETROX Joint Compound And Capped, Pad Coated With Oxide-Retardant, Overlap Crimps, Includes: PENETROX Joint Compound In Barrel And Oxide Retardant On Pad, Tools, Die Set Catalog Number, And (number Of Crimps): Y60BHU Tool, L735 Die, Conductor Type: ACAR, Aluminum, Die Index: 735, Tongue Angle: Straight

Product Details

General

Application	For ACAR And Stranded Aluminum Cable
Connector Type	Terminal
Die Index	735
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YNA-RT
UPC	781810016466
UPC 12 Digit	7818100164666

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	344 mm
Dimension - Length Overall inch	13.54 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.57 in
Dimension - Width fraction	3.57 in

Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2250 kcmil;2300 kcmil
Conductor - AL Str Size Range	2250 kcmil;2300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)