

# YNA7M10TH

by Burndy  
Catalog ID: YNA7M10TH

Prop 65 Notice

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #10, 3 #7 Alumoweld, 5/16 Steel, 7 Str., H/W Kit is available



## Product Details

### General

Connector Type	Terminal
Die Index	676;721
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
UPC	781810180518
UPC 12 Digit	7818101805188

### Dimensions

Dimension - B Length inch	2.68 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.5 in
Dimension - Outside Diameter inch	0.78 in
Dimension - Pad Width inch	1.5 in

### Conductor Related

Conductor - Galvanized Steel Str Size	5/16 (7) in
Conductor - Galvanized Steel Str Size Range	5/16 (7) in
Conductor Type	GAL Steel C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)