



YNA7M6T

by Burndy
Catalog ID: YNA7M6T

Prop 65 Notice

Al Compression Static Wire Terminal, 2 Holes, 7#6 Alumoweld, 1/2"(7 Str)
EHS Steel, 0.56" Hole Dia.

Product Details

General

Connector Type	Terminal
Die Index	679;789
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
UPC	781810016428
UPC 12 Digit	7818100164288

Dimensions

Dimension - B Length inch	4.10 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	249 mm
Dimension - Length Overall inch	9.8 in
Dimension - Outside Diameter inch	1.18 in
Dimension - Pad Width inch	1.5 in

Conductor Related

Conductor - Galvanized Steel Str Size	1/2 (19) in
Conductor - Galvanized Steel Str Size Range	1/2 (19) in
Conductor Type	GAL Steel C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)