


YNM428

by Burndy
Catalog ID: YNM428

HYCRAB 4 OUTLET 4/0 STR



Product Details

General

Material	Copper
Plated	Y
Plating Type	Tin - Hot Dipped
UPC	621945469228
UPC 12 Digit	781810101919

Dimensions

Dimension - B Length fraction	2 in
Dimension - Height fraction	3-3/16 in
Dimension - Height inch	3.19 in
Dimension - Length Overall inch	8.19 in

Conductor Related

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)