

YNS36R

by Burndy
Catalog ID: YNS36R

Prop 65 Notice

HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 500-556.5 Kcmil AL, 477 Kcmil ACSR, 230 kV



Product Details

General

Connector Type	Splice
Die Index	720
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810097465
UPC 12 Digit	7818100974655

Dimensions

Dimension - L Length Overall mm	234 mm
Dimension - Length Overall inch	9.2 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - ACSR Str Size	477 KCMIL
Conductor - ACSR Str Size Range	477 KCMIL
Conductor - AL Str Size	500 KCMIL - 556.5 KCMIL
Conductor - AL Str Size Range	500 KCMIL - 556.5 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)