

YNS39R

by Burndy
Catalog ID: YNS39R

Prop 65 Notice

HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 634.9-653.1 Kcmil ACAR, 600-650 Kcmil AL, 556.5 Kcmil ACSR, 2230 kV



Product Details

General

Connector Type	Splice
Die Index	722
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810085851
UPC 12 Digit	7818100858511

Dimensions

Dimension - L Length Overall mm	248 mm
Dimension - Length Overall inch	9.76 in
Dimension - Outside Diameter inch	1.50 in

Conductor Related

Conductor - ACAR Str Size Range	556.5 KCMIL
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil
Conductor - AL Str Size	600 kcmil - 650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)