

YNS451RTHT

by Burndy
Catalog ID: YNS451RTHT

Prop 65 Notice

Aluminium loop Hysplice, 715.5-874.5 kcmil ACSS, 18.60 in long



Product Details

General

Connector Type	Splice
Die Index	725
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810480311

Dimensions

Dimension - L Length Overall mm	472 mm
Dimension - Length Overall inch	18.6 in
Dimension - Outside Diameter inch	1.8 in

Conductor Related

Conductor - ACSR Str Size	715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/7) Mallard;874.5 (54/7) Crane
Conductor - AL Str Size	715.5;795.5;800;874.5

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)