

YNS451RT

by Burndy
Catalog ID: YNS451RT

Prop 65 Notice

HYSPLICE™ Al Tube Jumper Loop Sleeve, For EHV, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(Al), 715.5-874.5 kcmil(ACSR), 230 kV, 10.60" L, 725 Index



Product Details

General

Connector Type	Splice
Die Index	725
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016497
UPC 12 Digit	7818100164977

Dimensions

Dimension - Diameter Max Size inch	1.80 in
Dimension - L Length Overall mm	269 mm
Dimension - Length Overall inch	10.60 in
Dimension - Outside Diameter inch	1.80 in

Conductor Related

Conductor - ACAR Str Size Range	715.5 KCMIL - 874.5 KCMIL
Conductor - ACSR Str Size	715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) Starling kcmil-795 (54/7) Condor kcmil
Conductor - AL Str Size	795 KCMIL - 1000 KCMIL
Conductor - AL Str Size Range	795 KCMIL - 1000 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)