

YNS451R

by Burndy
Catalog ID: YNS451R

Prop 65 Notice

Al Tube Jumper Loop Sleeve, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(AL), 715.5-874.5 kcmil(ACSR), 10.04" L, For ACSR Cond.

Features: Jumper Sleeve For ACSR And Stranded Aluminum Cable Up To And Including 230 KV, Sleeve Is Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 725, Tools, Die Set Catalog Number, And (number Of Crimps): Y45 Tool, S725 Die, Y46 Tool, P725 Die, Y60BHU Tool, L725 Die, Conductor Type: ACSR, ACAR, Commercial Aluminum



Product Details

General

Application	For ACSR And Stranded Aluminum Cable Up To And Including 230 KV
Connector Type	Splice
Construction Material - Main	Aluminum
Die Index	725
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YNS-R
UPC	781810094495
UPC 12 Digit	7818100944955

Dimensions

Dimension - L Length Overall mm	255 mm
Dimension - Length Overall inch	10.04 in
Dimension - Outside Diameter inch	1.80 in

Conductor Related

Conductor - ACAR Str Size Range	840.2 kcmil-927.2 kcmil
Conductor - ACSR Str Size	715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil;874.5 (54/7) Crane kcmil
Conductor - ACSR Str Size Range	715.5 (54/7) Crow kcmil-874.5 (54/7) Crane kcmil
Conductor - AL Str Size	795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Size Range	750 kcmil-1000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)