

YNS52RT

by Burndy
Catalog ID: YNS52RT

Prop 65 Notice

HYSPLICE™, ACCOM: 1113 54-19 STR - 135 kcmil ACSR 1277-1280 kcmil
ACSR 1351.5-1510 kcmil AL INDEX: 728 T&B 189



Product Details

General

Connector Type	Splice
Die Index	728
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810180631
UPC 12 Digit	7818101806311

Dimensions

Dimension - Diameter Max Size inch	2.25 in
Dimension - L Length Overall mm	411 mm
Dimension - Length Overall inch	16.20 in
Dimension - Outside Diameter inch	2.25 in

Conductor Related

Conductor - ACAR Str Size Range	1277 KCMIL - 1280 KCMIL
Conductor - ACSR Str Size	1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil;1351.5 (54/19) Martin kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Finch kcmil-1351.5 (54/19) Martin kcmil
Conductor - AL Str Size	1351.5 KCMIL - 1510 KCMIL
Conductor - AL Str Size Range	1351.5 KCMIL - 1510 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)