

## YNS58RT

by Burndy  
Catalog ID: YNS58RT

Prop 65 Notice

HYSPLICE™, ACCOM: 1780kcmil ACSR 2000kcmil ALUM INDEX: BURNDY  
735 T&B 212,214



## Product Details

### General

Connector Type	Splice
Die Index	735
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810112748
UPC 12 Digit	7818101127488

### Dimensions

Dimension - Diameter Max Size inch	2.50 in
Dimension - L Length Overall mm	393 mm
Dimension - Length Overall inch	15.46 in
Dimension - Outside Diameter inch	2.50 in

### Conductor Related

Conductor - ACSR Str Size	1780 (84/19) Chukar kcmil
Conductor - ACSR Str Size Range	1780 (84/19) Chukar kcmil
Conductor - AL Str Size	2000 KCMIL
Conductor - AL Str Size Range	2000 KCMIL

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)