

YNS594RT

by Burndy
Catalog ID: YNS594RT

Prop 65 Notice

HYSPLICE™, ACCOM: 2300 KCMIL ACSR 2500 KCMIL ALUM 2267 KCMIL - 2500 KCMIL ACAR USE BURNDY DIE 740 OVERLAP CRIMPS



Product Details

General

Connector Type	Splice
Die Index	740
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810180655
UPC 12 Digit	7818101806555

Dimensions

Dimension - Diameter Max Size inch	2.60 in
Dimension - L Length Overall mm	420 mm
Dimension - Length Overall inch	16.53 in
Dimension - Outside Diameter inch	2.60 in

Conductor Related

Conductor - ACAR Str Size Range	2267 KCMIL - 2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)