

YNS594R

by Burndy
Catalog ID: YNS594R

Prop 65 Notice

HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 2267-2500 Kcmil ACAR, 2500 Kcmil AL, 2300 Kcmil ACSR, 230 kV



Product Details

General

Connector Type	Splice
Die Index	740
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810469774
UPC 12 Digit	7818104697744

Dimensions

Dimension - L Length Overall mm	357 mm
Dimension - Length Overall inch	14.04 in
Dimension - Outside Diameter inch	2.60 in

Conductor Related

Conductor - ACAR Str Size Range	2267 KCMIL - 2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)