

YNS59RT

by Burndy
Catalog ID: YNS59RT

Prop 65 Notice

HYSPLICE™, Al Tube Jumper Loop Sleeve, 2156 - 2167 Kcmil ACSR, 2250 - 2300 Kcmil Al, above 230 kV



Product Details

General

Connector Type	Splice
Die Index	735
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016473
UPC 12 Digit	7818100164733

Dimensions

Dimension - Diameter Max Size inch	2.50 in
Dimension - L Length Overall mm	385 mm
Dimension - Length Overall inch	15.14 in
Dimension - Outside Diameter inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil; 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2250 - 2300
Conductor - AL Str Size Range	2250 - 2300

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)