

YNT32R32R

by Burndy
Catalog ID: YNT32R32R

Prop 65 Notice

Two-piece aluminum compression T-Tap connector, 300-336.4 Kcmil ACSR, 336.4-350 Kcmil Aluminum, Tube to tube, 717 Index



Product Details

General

Connector Type	Tap
Die Index	717
Material	Aluminum
UPC	781810136416
UPC 12 Digit	7818101364166

Dimensions

Dimension - B Length inch	3.93 in
Dimension - Height fraction	6-23/59 in
Dimension - Height inch	6.39 in
Dimension - Length Overall inch	15.46 in
Dimension - Outside Diameter inch	1.19 in

Conductor Related

Conductor - ACSR Str Run	336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Run Range	336.4 (26/7) Linnet-336.4 (30/7) Oriole
Conductor - ACSR Str Size	336.4 (26/7) kcmil;336.4 (30/7) kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) kcmil-336.4 (30/7) kcmil
Conductor - ACSR Str Tap	300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Tap Range	300.0 (26/7) Ostrich kcmil-336.4 (30/7) Oriole kcmil
Conductor - AL Str Run	336.4;350
Conductor - AL Str Run Range	336.4-350
Conductor - AL Str Tap	336.4;350
Conductor - AL Str Tap Range	336.4-350

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)