

YNT36R36R

by Burndy
Catalog ID: YNT36R36R

Prop 65 Notice

Compression T-Taps, ACCOM: RUN & TAP 477 kcmil ACSR 500-556.5
kcmil AL DIE INDEX: 720



Product Details

General

Connector Type	Tap
Die Index	720
Material	Aluminum
UPC	781810069073
UPC 12 Digit	7818100690733

Dimensions

Dimension - B Length inch	4.19 in
Dimension - Height fraction	6-17/20 in
Dimension - Height inch	6.85 in
Dimension - Length Overall inch	16.29 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - ACSR Str Run	477.0 (24/7) Flicker;477.0 (26/7) Hawk
Conductor - ACSR Str Run Range	477.0 (24/7) Flicker-477.0 (26/7) Hawk
Conductor - ACSR Str Size	477.0 (24/7) kcmil;477.0 (26/7) kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) kcmil-477.0 (26/7) kcmil
Conductor - ACSR Str Tap	477.0 (18/1) Perlican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Tap Range	477.0 (18/1) Perlican-477.0 (30/7) Hen
Conductor - AL Str Run	500;550;556.5
Conductor - AL Str Tap	500;550;556.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)