

YNT49R49RHT

by Burndy
Catalog ID: YNT49R49RHT

Aluminum Compression Two piece T-Tap connector, 230 kV, 1033.5-1272 kcmil Aluminum, 2 Pad holes



Product Details

General

Connector Type	Tap
Die Index	L727
UPC	781810488027
UPC 12 Digit	7818104880277

Dimensions

Dimension - Height inch	10.54
Dimension - Length Overall inch	25.66 in

Electrical Ratings

Voltage Rating	230 kV
----------------	--------

Conductor Related

Conductor - ACSR Str Run Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - ACSR Str Tap Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - AL Str Run Range	1033.5 kcmil-1272 kcmil
Conductor - AL Str Tap Range	1033.5 kcmil-1272 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)