

YNT49R49RT

by Burndy
Catalog ID: YNT49R49RT

Prop 65 Notice

Two-piece aluminum compression T-Tap connector, 900-1113 Kcmil ACSR, 1033.5-1272 Kcmil Aluminum, Tube to tube, 727 Index



Product Details

General

Connector Type	Tap
Die Index	727
Material	Aluminum
UPC	781810180709
UPC 12 Digit	7818101807099

Dimensions

Dimension - B Length inch	4.57 in
Dimension - Height fraction	7-9/10 in
Dimension - Height inch	7.9 in
Dimension - Length Overall inch	17.66 in
Dimension - Outside Diameter inch	1.97 in

Conductor Related

Conductor - ACSR Str Run	900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch
Conductor - ACSR Str Run Range	900 (54/7) Canary-1113 (54/19) Finch
Conductor - ACSR Str Tap	900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch
Conductor - ACSR Str Tap Range	900 (54/7) Canary-1113 (54/19) Finch
Conductor - AL Str Run	1033.5;1100;1192.5;1200;1272.2
Conductor - AL Str Run Range	1033.5-1272.2
Conductor - AL Str Tap	1033.5;1100;1192.5;1200;1272.2
Conductor - AL Str Tap Range	1033.5-1272.2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)